

CIRCULUM®

X-ROe

DESCRIPTION

X-ROe is an expandable polystyrene grade containing pentane as a blowing agent. The products are delivered in the form of spherical beads with a bulk density of about 0.6 g/cm³. X-GWW is available in 1050 kg octabins.

APPLICATIONS

The properties of X-ROe make it suitable for use in waterfiltration approved by OTV, the application is prefoamed beads with a density and a BSD according spec's in table on the next sheet. Tradename for OTV for prefoamed beads is Biostyrene

PROCESSING

The processing conditions of **X-ROe** depend on the combination of the product and processing equipment used. Optimal settings have to be adjusted for each combination. Some general processing conditions are given below:

Prefoaming	The steam has to be mixed with air to reach temperatures of 90-100 °C, to reach densities 45-55 kg/m ³ , batch prefoamer is recommended
Conditioning	Depends on the density. The higher the density the longer the conditioning time. Generally 12–24 hours is recommended.
Moulding	The end-use of the products is pre-foamed beads. Molding is possible but the coating of the beads is optimized for only prefoaming.

STORAGE

X-ROe should be stored at below 20 °C. Protect from direct sunlight and other weather conditions (rain, wind, frost etc.). Keep away from any source of ignition. The storage time should not exceed three months. After opening of the packaging, it should be used as soon as possible.

SAFETY

In transport **X-ROe** is classified according to European regulations for product transport: Substance number UN2211, Class 9.

In processing avoid generating dust. All equipment should be properly earthen. Releases pentane during processing which might form a flammable/explosive vapour-air mixture. Use proper ventilation and keep away from any source of ignition. A Safety Data Sheet is available on request.

TECHNICAL INFORMATION

TYPICAL PHYSICAL PROPERTIES

Raw material

	<u>Value</u>	<u>Unit</u>	<u>Test method</u>
Pentane content	> 4.5	%	Gas chromatography
Main bead size distribution	see table below		Image analyser

SPECIFICATION OTV Grades					
					concept
	Bewi Synbra	1417ROX	1619ROX	1822ROX	1923ROX
Mmean beadsizes (mm) EPS beads		1,58 mm	1,83 mm	2,00 mm	2,2 mm
beadsizes distribution (µm)	spec mean beadsizes IA	1510-1650	1750-1910	1910-2090	2050 - 2 300
	95% beads between IA	1250 - 1750	1400-1950	1 650 - 2 250	1 900 - 2 450
	5% between IA	950 - 1250	1200-1400	1350 - 1 650	1 550 - 1 900
	0,02 % smaller than IA				
	0,03% bigger than IA				
	max.0,05% smaller than SA	900	1.180	1,350	1,55
	max. 0,1% bigger than SA	1.800	2.000	2.250	2,45
Fines =< (parts)	50	50	50	50	
Blowing agent (%)		>=4,0	>=4,0	>=4,0	>=4,1
	IA = Image Analyses				
	SA= Sieve Analyses				

RECYCLING

X-ROe is suitable for recycling using modern methods of grinding, cleaning and regranulation.

In-house production waste should be kept clean to facilitate direct recycling.

Please contact your BEWI representative for more details on various aspects of safety, recovery and disposal of the product.

This information is not to be taken as a warranty or representation for which BEWI assumes legal responsibility nor as permission or recommendation to practice any patented invention without a license. It is offered solely for your consideration, investigation, verification and shall form no part of any contract with a customer.

La présente documentation n'engage pas notre responsabilité et n'autorise en aucune façon l'usage sans contrat de licence d'inventions brevetées. Les termes du présent rapport doivent être considérés comme une simple indication, sujette aux vérifications d'usage.

Bei diesen Angaben handelt es sich weder um eine Garantie-Erklärung oder Darstellung, für die wir eine rechtliche Haftung übernehmen, noch um eine Erlaubnis oder Empfehlung, irgendeine patentierte Erfindung ohne Lizenz auszuwerten. Die Informationen werden Ihnen lediglich zu Ihrer Erwägung, Untersuchung und Überprüfung übermittelt und sind nicht Bestandteil von Verträgen mit Kunden.

Uppgifter i datablad, broschyrer och annat informationsmaterial ges som vägledning och är ej bindande för BEWI.

Tässä esitteessä ja muussa tiedotusaineistossa annettut tekniset tiedot ovat suuntaa antavia, eivätkä ne ole BEWI :tä sitovia.

Le informazioni contenute nelle schede tecniche, bollettini ed altro materiale informativo corrispondono all'attuale livello di conoscenza e intendono fornire indicazioni sui prodotti BEWI e le loro possibilità di impiego. Non sono pertanto da intendersi come garanzia.